



Ledinaire All-in floodlights

BVP167 LED36/830_40_65 PSU 30W SWB MDU

Ledinaire All-in floodlights, 30 W, 3300 lm, 3600 lm, 3000 K, 4000 K, 6500 K, CRI80, Sensor-controlled on/off, Symmetrical, MDU1, IP65

With this Ledinaire all-in floodlights range, you can easily adjust the color temperature by a simple switch. No need to choose between warm white, neutral white or cool white anymore, you get all these in one single product! The range comes with the Philips high quality levels at a competitive price. Reliable, energy-efficient and affordable – just what you need.

Product data

General Information		Operating and Electrical	
Lamp family code	LED36S [LED module, system flux 3600 lm]	Correlated Colour Temperature (Nom)	3000 4000 6500 K
Number of gear units	Unit	Luminous efficacy (rated) (nom.)	120 110 lm/W
Driver included	Yes	Colour rendering index (CRI)	>80
Light source engine type	LED system in flux	Light source colour	Multi Colour Temperature
Value ladder	Value	Optic type	Symmetric 110°
Serviceability class	Class C, luminaire without serviceable parts, not serviceable	Luminaire light beam spread	110°
Warranty period	5 years	Optic type outdoor	Symmetrical
Sustainability rating	Unclassified	All-in Type	All-in, Multi Color Temperature
		Effective projected area	0.016965 m²
Light Technical			
Upwards light output ratio	0	Input Voltage	220-240 V
Luminous Flux	3,300 3,600 lm	Line Frequency	50 or 60 Hz
		Inrush current	1.22 A

Ledinaire All-in floodlights

Inrush time	0.0072 ms
Power Consumption	30 W
Power Factor (Fraction)	0.9
Connection	Flying leads/cables
Cable	Cable 1.0 m without plug
Number of products on MCB (16 A type B)	73
Suitable for random switching	Not applicable
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 1.5 kV differential mode and 1.5 kV common mode
Total harmonic distortion	20 %

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	Sensor-controlled on/off
Constant light output	No
Embedded control	Movement and light sensor (On/Off)
Photocell	Photocell included

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Glass
Optical cover/lens material	Tempered glass
Fixation material	Steel
Housing Colour	Grey
Mounting device	Via U Shaped Bracket, Aiming Scale Angle, Universal Installation
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	220 mm
Overall width	133 mm
Overall height	56 mm
Dimensions (height x width x depth)	56 x 133 x 220 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Standard tilt angle post-top	27°
Standard tilt angle side entry	-
Optical cover type	Glass
Net Weight (Piece)	0.585 kg

Emergency Operation

Central Emergency	No
-------------------	----

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Flickering value (PstLM)	1
Ambient temperature range	-25 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.440,0.403); (0.369,0.364); (0.313,0.337) SDCM<5
Power consumption tolerance	+/-10%
Init. Colour Rendering Index Tolerance	-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	7.5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L80
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L70

Product Data

Order product name	BVP167 LED36/830_40_65 PSU 30W SWB MDU
Full product name	BVP167 LED36/830_40_65 PSU 30W SWB MDU
Full EOC	872016973617799
Order code	911401893386
Material no. (12 NC)	911401893386
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169736177
Numerator – packs per outer box	16
EAN/UPC - Case	8720169736368

Ledinaire All-in floodlights

Dimensional drawing



mm	10W	20W	30W	50W	70W
A	70	82	117	150	175
B	174	191	220	255	295
C	58	58	58	58	70
D	90	109	145	185	215
E	4,2	4,2	4,5	5,5	6,5
F	4,2	4,2	4,5	6,5	6,5
G	85	97	133	173	203
H	41	50	70	90	110
I	51	60	85	116	130

