

BN126C LED41S/840 PSU L1200

911401898980



Coreline Slim Batten, 31 W, 4100 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

General Information

Light source engine type	LED
Service tag	Yes

Light Technical

Luminous Flux	4,100 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	31 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	45
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	No
Control interface	-


Mechanical and Housing

Housing Material	Steel
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	1,135 mm
Overall width	65 mm
Overall height	65 mm
Dimensions (Height x Width x Depth)	65 x 65 x 1135 mm
Ingress protection code	IP20/40 [Finger-protected;Wire-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	Polycarbonate Diffuser
Net Weight (Piece)	0.850 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 to +40 °C

Dimensional drawing



Related Documents

Documents and certificates	Document Name	Download
Installation Instructions	BN126C-MI.pdf	Download 

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	BN126C LED41S/840 PSU L1200
Full product name	BN126C LED41S/840 PSU L1200
Full product code	692382863853599
Order code	911401898980
Material Nr. (12NC)	911401898980
Local order code	BN12641L8404FT
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638535
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828638597

