



# Essential Smartbright Wide Batten BN005C

## BN005C LED22/NW L600 PSU GM

Essential Smartbright Wide Batten BN005C, 20 W, 2200 lm, 4000 K, Symmetrical

Philips Essential smartbright wide batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 2 standard sizes, it has option of 3 CCTs to suit different requirements.

### Product data

General Information		Unified glare rating CEN	
Number of gear units	1 unit		Not applicable
Gear	EB [Electronic]	Effective projected area	0.75 m <sup>2</sup>
Driver included	Yes	<b>Operating and Electrical</b>	
Light source engine type	LED	Input Voltage	220 to 240 V
Value ladder	Value	Line Frequency	50 or 60 Hz
Warranty period	2 years	Inrush current	30 A
<b>Light Technical</b>		Inrush time	0.015 ms
Luminous Flux	2.200 lm	Power Consumption	20 W
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	0.5
Luminous Efficacy (rated) (Nom)	110 lm/W	Connection	-
Color rendering index (CRI)	≥80	Cable	Cable 0.2 m without plug
Number of light sources	1	Number of products on MCB of 16 A type B	96
Beam angle of light source	115 degree(s)	Suitable for random switching	No
Light source color	840 neutral white	Protection class IEC	Safety class II
Optic type	Symmetrical	<b>Controls and Dimming</b>	
Luminaire light beam spread	115°	Dimmable	-

# Essential Smartbright Wide Batten BN005C

Control interface	-
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Mounting bracket
Optical cover finish	-
Overall length	600 mm
Overall width	70 mm
Overall height	27 mm
Dimensions (Height x Width x Depth)	27 x 70 x 600 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Opal
Net Weight (Piece)	0.150 kg

## Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	No

ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	(0.38, 0.38) SDCM≤6
Power consumption tolerance	+/-10%

## Product Data

Order product name	BN005C LED22/NW L600 PSU GM
Full product name	BN005C LED22/NW L600 PSU GM
Full product code	871951496187699
Order code	96187699
Material Nr. (12NC)	911401899184
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514961876
Numerator - Packs per outer box	50
EAN/UPC - Case	8719514961999

## Dimensional drawing

