



CitySoul gen2 LED Mini

BPP530 LED60-4S/830 II DM50 D9 AL GR

CitySoul gen2 LED Mini, Urban road & street light, 46.5 W, 5100 lm, 3000 K, CRI80, DALI, Distribution medium 50, Safety class II, IP66, STD

CitySoul LED gen2 is one of our most versatile and iconic luminaires, designed to bring elegance, efficiency, and ambience to every cityscape. Its rounded, minimalist form with seamless bracket transitions creates a coherent identity across residential areas, main roads, and vibrant city centers. This modular family offers multiple sizes, mounting, and bracket options—giving lighting designers the flexibility to adapt to any urban environment without compromising on aesthetics. Powered by our proven LEDGINE-O platform and now enhanced with the innovative LEDGINE-P for even higher efficacy, CitySoul LED gen2 delivers the right light, exactly where it's needed. Application-specific optics ensure safety, comfort, and reduced energy use, while dedicated light recipes preserve dark skies and support healthier ecosystems. With one or two System Ready (SR) sockets, CitySoul LED gen2 is fully prepared for connected lighting and advanced control platforms such as Interact, helping municipalities unlock further energy savings, operational insights, and long-term sustainability.

Product data

General information		Service tag	
Lamp family code	LED60 [LED module 6000 lm]	Lighting Technology	LED
Light source replaceable	Yes	Value ladder	Performance
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes		
Light source engine type	LED		

CitySoul gen2 LED Mini

Light Technical	
Upward light output ratio	0.03
Luminous Flux	5,100 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	80
Number of light sources	30
Light source color	830 warm white
Luminaire light beam spread	-
Optic type outdoor	Distribution medium 50
Effective projected area	0.05 m ²

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	46.5 W
Power Factor (Fraction)	0.98
Connection	Screw connection block
Cable	-
Number of products on MCB of 16 A type B	11
Protection class IEC	Safety class II
Surge Protection (Common/Differential)	Standard surge protection level

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI
Maximum dim level	10%

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	Acrylate
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Post-top for diameter 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall height	165 mm
Overall diameter	630 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Optical cover type	Clear glass

Net Weight (Piece)	12.700 kg
Approval and Application	
Flammability mark	-
CE mark	Yes
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Ambient temperature range	-40 to +50 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43, 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤5

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L97

Sustainability Data	
Sustainability rating	Unclassified
Embedded carbon (A1-A3)	113 kg CO ₂ e
Product non-virgin material ratio	48.5 %
Recyclable content ratio of the finished product	59.8 %

GWP total B6 (kg CO₂eq) Declared Unit Please calculate using your local energy mix value: Power Declared Unit (kW) * Service life (hrs) Declared Unit * Energy mix (kg CO₂eq / kwh)


GWP total B6 (kg CO₂eq) Functional Unit Please calculate using your local energy mix value: Power Declared Unit (kW) * 1000 (lm) / Lumen output (lm) Declared Unit * 35000 (hrs) * Energy mix (kg CO₂eq / kwh)

Product Data	
Order product name	BPP530 LED60-4S/830 II DM50 D9 AL GR
Full product name	BPP530 LED60-4S/830 II DM50 D9 AL GR
Full product code	871869987865800
Order code	912300024408
Material Nr. (12NC)	912300024408
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699878658
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699878658


CitySoul gen2 LED Mini

Product family code BPP530 [CitySoul gen2 Mini]

Dimensional drawing



Photometric data



Polar Normal (separate) - BPP530I - 912300024408

