



Emergency downlight EM120B

EM120B LED2S EL3 WH

Emergency lighting 3 hours duration Pro version, White

Polycarbonate, White, Power supply unit (On/Off), 180 lm, 4 W, 90 lm/W, 5000 K, (0.34, 0.35) SDCM<3, Very wide beam, Clear, Polycarbonate, IP20 | Finger-protected, IK02 | 0.2 J standard, Safety class II, Push-in connector 2-pole, Emergency lighting 3 hours duration Pro version

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Service tag	No
Lighting Technology	LED
Mounting	Recessed
Warranty period	3 years
Light Technical	
Luminous Flux	180 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	>70
Beam angle of light source	105 degree(s)
Light source color	750 neutral white
Optic type	Very wide beam
Luminaire light beam spread	105°

Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	4 W
Inrush current	8.7 A
Inrush time	125 ms
Power Consumption	4 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 2-pole
Cable	-
Number of products on MCB of 16 A type B	40
Suitable for random switching	No
Protection class IEC	Safety class II

Emergency downlight EM120B

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable
Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	620 mm
Overall width	33 mm
Overall height	45 mm
Overall diameter	80 mm
Dimensions (Height x Width x Depth)	45 x 33 x 620 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Net Weight (Piece)	0.335 kg
Emergency Operation	
Rated duration of the emergency lighting (when fully charged)	3 hour(s)
Central Emergency	No
Emergency lighting	Emergency lighting 3 hours duration Pro version
Emergency function testing method	Manual / Test button
Emergency lighting operation mode	Non-maintained
Approval and Application	
Glow-wire test	-
Flammability mark	-
CE mark	Yes
ENEC mark	-
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	1.6
Ambient temperature range	0 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.34, 0.35) SDCM<3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.8 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L70
Sustainability Data	
Sustainability rating	Unclassified
Repair class	Repair Class D, this product is not designed to be repaired.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic
Product Data	
Order product name	EM120B LED2S EL3 WH
Full product name	EM120B LED2S EL3 WH
Full product code	871869979146999
Order code	912401483241
Material Nr. (12NC)	912401483241
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699791469
Numerator - Packs per outer box	20
EAN/UPC - Case	8718699791506

Emergency downlight EM120B

Dimensional drawing

