



# Cleanroom CR350B

## CR350B LED60S/940 PSU W60L60

Cleanroom CR350B, ISO 14644-1 Air cleanliness Class 1, 60 W, 600x600 mm, 6000 lm, 4000 K, CRI>90, UGR19

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

### Product data

General Information		Warranty period	
Light source replaceable	No	5 years	
Number of gear units	1 unit	Sustainability rating	
Driver included	Yes	Unclassified	
Service tag	Yes	Light Technical	
Lighting Technology	LED	Luminous Flux	6,000 lm
Value ladder	Specification	Saturated Red (R9)	>50
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection device, optics, front cover and mechanical parts	Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	100 lm/W
		Color rendering index (CRI)	>90
		Beam angle of light source	120 degree(s)
		Light source color	940 neutral white

# Cleanroom CR350B

Optic type	Wide beam
Luminaire light beam spread	80° x 80°
Unified glare rating CEN	19

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	- W
Inrush current	20 A
Inrush time	240 ms
Power Consumption	60 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	24
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	6 %

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover material	Glass
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	595 mm
Overall width	595 mm
Overall height	90 mm
Dimensions (Height x Width x Depth)	90 x 595 x 595 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK09 [10 J]
Net Weight (Piece)	7.300 kg

## Approval and Application

Glow-wire test	-
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.39, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

## Product Data


Order product name	CR350B LED60S/940 PSU W60L60
Full product name	CR350B LED60S/940 PSU W60L60
Full product code	871869979713300
Order code	912401483360
Material Nr. (12NC)	912401483360
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699797133
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699797133

# Cleanroom CR350B

## Dimensional drawing



## Photometric data



Polar Normal (separate) - null - 912401483360

