



# Cleanroom CR350B

## CR350B LED60S/940 PSD W60L60 OC

Cleanroom CR350B, ISO 14644-1 Air cleanliness Class 1, 60 W, 600x600 mm, 6000 lm, 4000 K, CRI>90, DALI, UGR19

ISO 14644-1 Air cleanliness Class 1, 600x600 mm, Steel, White, Traffic white (RAL9016), Power supply unit with DALI interface, 6000 lm, 60 W, 100 lm/W, 4000 K, (0.39, 0.38) SDCM <3, CRI>90, UGR19, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK09 | 10 J, Safety class I, Push-in connector 5-pole

### Product data

General Information		Luminaire light beam spread	
Light source replaceable	No	Luminaire light beam spread	80° x 80°
Number of gear units	1 unit	Unified glare rating CEN	19
Driver included	Yes	Operating and Electrical	
Service tag	Yes	Input Voltage	220 to 240 V
Lighting Technology	LED	Line Frequency	50 to 60 Hz
Value ladder	Specification	Average CLO power consumption	- W
Warranty period	5 years	Inrush current	24.9 A
		Inrush time	215 ms
		Power Consumption	60 W
		Power Factor (Fraction)	0.9
		Connection	Push-in connector 5-pole
		Cable	-
		Number of products on MCB of 16 A type B	24
		Suitable for random switching	No
		Protection class IEC	Safety class I
		Total harmonic distortion	20 %
Light Technical			
Luminous Flux	6,000 lm		
Saturated Red (R9)	>50		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	100 lm/W		
Color rendering index (CRI)	>90		
Beam angle of light source	120 degree(s)		
Light source color	940 neutral white		
Optic type	Wide beam		

# Cleanroom CR350B

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover material	Glass
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	595 mm
Overall width	595 mm
Overall height	90 mm
Dimensions (Height x Width x Depth)	90 x 595 x 595 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Net Weight (Piece)	7.300 kg

## Approval and Application

Glow-wire test	-
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	(0.39, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

## Sustainability Data


Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

## Product Data


Order product name	CR350B LED60S/940 PSD W60L60
Full product name	CR350B LED60S/940 PSD W60L60 OC
Full product code	871869979716400
Order code	79716400
Material Nr. (12NC)	912401483363
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699797164
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699797164

# Cleanroom CR350B

## Dimensional drawing



## Photometric data



Polar Normal (separate) - 912401483363

