



Cleanroom CR350B

CR350B LED60S/940 PSD W60L60

Cleanroom CR350B, ISO 14644-1 Air cleanliness Class 1, 60 W, 600x600 mm, 6000 lm, 4000 K, CRI>90, DALI, UGR19

ISO 14644-1 Air cleanliness Class 1, 600x600 mm, Steel, White, Traffic white (RAL9016), Power supply unit with DALI interface, 6000 lm, 60 W, 100 lm/W, 4000 K, (0.39, 0.38) SDCM <3, CRI>90, UGR19, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK09 | 10 J, Safety class I, Push-in connector 5-pole

Product data

General Information		Luminaire light beam spread	
Light source replaceable	No		80° × 80°
Number of gear units	Unit	Unified Glare Rating (CEN)	19
Driver included	Yes	Operating and Electrical	
Service Tag	Yes	Input Voltage	220 to 240 V
Lighting Technology	LED	Line Frequency	50 to 60 Hz
Value ladder	Specification	Average CLO power consumption	- W
Warranty period	5 years	Inrush current	24.9 A
		Inrush time	215 ms
		Power Consumption	60 W
		Power Factor (Fraction)	0.9
		Connection	Push-in connector 5-pole
		Cable	-
		Number of products on MCB (16 A type B)	24
		Suitable for random switching	No
		Protection class IEC	Safety class I
		Total harmonic distortion	20 %

Cleanroom CR350B

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI standard	DALI-2™
Maximum dim level	1%

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover/lens material	Glass
Fixation material	-
Housing Colour	White
Optical cover/lens finish	Clear
Overall length	595 mm
Overall width	595 mm
Overall height	90 mm
Dimensions (height x width x depth)	90 x 595 x 595 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Net Weight (Piece)	7.300 kg

Approval and Application

Glow-wire test	-
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.39, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80


Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.

Product Data


Order product name	CR350B LED60S/940 PSD W60L60
Full product name	CR350B LED60S/940 PSD W60L60
Full EOC	871869979716400
Order code	912401483363
Material no. (12 NC)	912401483363
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718699797164
Numerator – packs per outer box	1
EAN/UPC - Case	8718699797164

Dimensional drawing



Cleanroom CR350B

Photometric data



Polar Normal (separate) - 912401483363

