



# Cleanroom CR350B

## CR350B LED40S/940 PSU W30L120

Cleanroom CR350B, ISO 14644-1 Air cleanliness Class 1, 41 W, 1200x300 mm, 4000 lm, 4000 K, CRI>90, UGR19

ISO 14644-1 Air cleanliness Class 1, 1200x300 mm, Steel, White, Traffic white (RAL9016), Power supply unit (On/Off), 4000 lm, 41 W, 98 lm/W, 4000 K, (0.39, 0.38) SDCM <3, CRI>90, UGR19, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK09 | 10 J, Safety class I, Push-in connector 3-pole

### Product data

| General Information                |                   |
|------------------------------------|-------------------|
| Light source replaceable           | No                |
| Number of gear units               | 1 unit            |
| Driver included                    | Yes               |
| Service tag                        | Yes               |
| Lighting Technology                | LED               |
| Value ladder                       | Specification     |
| Warranty period                    | 5 years           |
| Light Technical                    |                   |
| Luminous Flux                      | 4,000 lm          |
| Saturated Red (R9)                 | >50               |
| Correlated Color Temperature (Nom) | 4000 K            |
| Luminous Efficacy (rated) (Nom)    | 98 lm/W           |
| Color rendering index (CRI)        | >90               |
| Beam angle of light source         | 120 degree(s)     |
| Light source color                 | 940 neutral white |
| Optic type                         | Wide beam         |
| Luminaire light beam spread        | 80° x 80°         |

| Unified glare rating CEN                 | 19                       |
|--|--------------------------|
| Operating and Electrical                 |                          |
| Input Voltage                            | 220 to 240 V             |
| Line Frequency                           | 50 to 60 Hz              |
| Average CLO power consumption            | - W                      |
| Inrush current                           | 20 A                     |
| Inrush time                              | 240 ms                   |
| Power Consumption                        | 41 W                     |
| Power Factor (Fraction)                  | 0.9                      |
| Connection                               | Push-in connector 3-pole |
| Cable                                    | -                        |
| Number of products on MCB of 16 A type B | 24                       |
| Suitable for random switching            | No                       |
| Protection class IEC                     | Safety class I           |
| Total harmonic distortion                | 6 %                      |
| Controls and Dimming                     |                          |
| Dimmable                                 | No                       |

# Cleanroom CR350B

|                               |                            |
|-------------------------------|----------------------------|
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Control interface             | -                          |
| Constant light output         | No                         |
| Maximum dim level             | Not applicable             |

## Mechanical and Housing

|                                     |  |
|-------------------------------------|--|
| Housing Material                    | Steel  |
| Reflector material                  | -  |
| Optic material                      | Polystyrene                                  |
| Optical cover material              | Glass  |
| Fixation material                   | -  |
| Housing Color                       | White  |
| Optical cover finish                | Clear  |
| Overall length                      | 1,195 mm                                     |
| Overall width                       | 295 mm                                       |
| Overall height                      | 100 mm                                       |
| Dimensions (Height x Width x Depth) | 100 x 295 x 1195 mm                          |
| Ingress protection code             | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code        | IK09 [10 J]                                  |
| Net Weight (Piece)                  | 7.500 kg                                     |

## Approval and Application

|                                    |  |
|------------------------------------|--|
| Glow-wire test                     | -  |
| Flammability mark                  | For mounting on normally flammable surfaces    |
| CE mark                            | Yes  |
| ENEC mark                          | ENEC mark                                      |
| Photobiological risk               | Photobiological risk group 0 @200mm to EN62778 |
| EU RoHS compliant                  | Yes  |
| Performance ambient temperature Tq | 25 °C  |
| Ambient temperature range          | -20 to +35 °C                                  |

## Initial Performance (IEC Compliant)

|                         |        |
|-------------------------|--------|
| Luminous flux tolerance | +/-10% |
|-------------------------|--------|

|  |                      |
|--|----------------------|
| Initial chromaticity                                   | (0.39, 0.38) SDCM <3 |
| Power consumption tolerance                            | +/-10%               |
| Standard Deviation of Colour Matching (McAdam ellipse) | SDCM≤3               |

## Over Time Performance (IEC Compliant)

|  |     |
|--|-----|
| Control gear failure rate at median useful life 50000 h              | 5 % |
| Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h | L80 |


## Sustainability Data

|  |  |
|--|--|
| Sustainability rating                      | Unclassified   |
| Repair class                               | Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time. |
| Non-virgin material ratio of the packaging | Cardboard > 80% recycled Plastic >35% recycled   |
| Packaging Recyclable content ratio         | Cardboard recycling rate > 80% Plastic recycling rate > 40%  |
| Packaging Material                         | Cardboard Plastic  |

## Product Data


|                                 |                               |
|---------------------------------|-------------------------------|
| Order product name              | CR350B LED40S/940 PSU W30L120 |
| Full product name               | CR350B LED40S/940 PSU W30L120 |
| Full product code               | 871869979719500               |
| Order code                      | 912401483366                  |
| Material Nr. (12NC)             | 912401483366                  |
| Numerator - Quantity Per Pack   | 1                             |
| EAN/UPC - Product/Case          | 8718699797195                 |
| Numerator - Packs per outer box | 1                             |
| EAN/UPC - Case                  | 8718699797195                 |

## Dimensional drawing



# Cleanroom CR350B

## Photometric data



Polar Normal (separate) - 912401483366

