



# Cleanroom CR350B

## CR350B LED40S/940 PSU W30L120

Cleanroom CR350B, ISO 14644-1 Air cleanliness Class 1, 41 W, 1200x300 mm, 4000 lm, 4000 K, CRI>90, UGR19

When operating a facility where the highest levels of hygiene are required, the demands placed on light are also very high. It must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips Cleanroom CR350B luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and color rendering, these Philips cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

### Product data

General Information			
Light source replaceable	No		protection device, optics, front cover and mechanical parts
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Sustainability rating	Unclassified
Service tag	Yes		
Lighting Technology	LED	Light Technical	
Value ladder	Specification	Luminous Flux	4,000 lm
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge	Saturated Red (R9)	>50
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	98 lm/W
		Color rendering index (CRI)	>90

# Cleanroom CR350B

Beam angle of light source	120 degree(s)
Light source color	940 neutral white
Optic type	Wide beam
Luminaire light beam spread	80° x 80°
Unified glare rating CEN	19

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Average CLO power consumption	- W
Inrush current	20 A
Inrush time	240 ms
Power Consumption	41 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	24
Suitable for random switching	No
Protection class IEC	Safety class I
Total harmonic distortion	6 %

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Maximum dim level	Not applicable

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover material	Glass
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	1,195 mm
Overall width	295 mm
Overall height	100 mm
Dimensions (Height x Width x Depth)	100 x 295 x 1195 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]

Mech. impact protection code	IK09 [10 J]
Net Weight (Piece)	7.500 kg

## Approval and Application

Glow-wire test	-
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.39, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life	5 %
50000 h	
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80

## Product Data


Order product name	CR350B LED40S/940 PSU W30L120
Full product name	CR350B LED40S/940 PSU W30L120
Full product code	871869979719500
Order code	912401483366
Material Nr. (12NC)	912401483366
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699797195
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699797195

# Cleanroom CR350B

## Dimensional drawing



## Photometric data



Polar Normal (separate) - null - 912401483366

