



# Cleanroom CR350B

## CR350B LED60S/840 PSD W30L120 OC

Cleanroom CR350B, ISO 14644-1 Air cleanliness Class 1, 55 W, 1200x300 mm, 6000 lm, 4000 K, DALI, UGR19

ISO 14644-1 Air cleanliness Class 1, 1200x300 mm, Steel, White, Traffic white (RAL9016), Power supply unit with DALI interface, 6000 lm, 55 W, 109 lm/W, 4000 K, (0.38, 0.38) SDCM <3, UGR19, Wide beam, Clear, Glass, IP65 | Dust penetration-protected, jet-proof, IK09 | 10 J, Safety class I, Push-in connector 5-pole

### Product data

General Information		Unified glare rating CEN	
Light source replaceable	No		19
Number of gear units	1 unit	Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Service tag	Yes	Line Frequency	50 to 60 Hz
Lighting Technology	LED	Average CLO power consumption	- W
Value ladder	Specification	Inrush current	24.9 A
Warranty period	5 years	Inrush time	215 ms
Light Technical		Power Consumption	55 W
Luminous Flux	6,000 lm	Power Factor (Fraction)	0.9
Saturated Red (R9)	<50	Connection	Push-in connector 5-pole
Correlated Color Temperature (Nom)	4000 K	Cable	-
Luminous Efficacy (rated) (Nom)	109 lm/W	Number of products on MCB of 16 A type B	24
Color rendering index (CRI)	>80	Suitable for random switching	No
Beam angle of light source	120 degree(s)	Protection class IEC	Safety class I
Light source color	840 neutral white	Total harmonic distortion	20 %
Optic type	Wide beam	Controls and Dimming	
Luminaire light beam spread	80° x 80°	Dimmable	Yes

# Cleanroom CR350B

Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
DALI Standard	DALI-2™
Maximum dim level	1%

## Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Polystyrene
Optical cover material	Glass
Fixation material	-
Housing Color	White
Optical cover finish	Clear
Overall length	1,195 mm
Overall width	295 mm
Overall height	100 mm
Dimensions (Height x Width x Depth)	100 x 295 x 1195 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Net Weight (Piece)	7.500 kg

## Approval and Application

Glow-wire test	-
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	ENEC mark
Photobiological risk	Photobiological risk group 0 @200mm to EN62778
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-10%
Standard Deviation of Colour Matching (McAdam ellipse)	SDCM≤3

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L80


## Sustainability Data

Sustainability rating	Unclassified
Repair class	Repair Class B, the driver and light source of this luminaire can be replaced by a service technician. Parts and documentation are available for an extended period of time.
Non-virgin material ratio of the packaging	Cardboard > 80% recycled Plastic >35% recycled
Packaging Recyclable content ratio	Cardboard recycling rate > 80% Plastic recycling rate > 40%
Packaging Material	Cardboard Plastic

## Product Data

Order product name	CR350B LED60S/840 PSD W30L120
Full product name	CR350B LED60S/840 PSD W30L120 OC
Full product code	871869979726300
Order code	79726300
Material Nr. (12NC)	912401483373
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699797263
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699797263

## Dimensional drawing



# Cleanroom CR350B

## Photometric data



Polar Normal (separate) - 912401483373

