



# Cleanroom CR350B

## CR350Z SMB W60L60

Cleanroom CR350B, Accessory, Steel, White

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

### Product data

General Information	
Value ladder	Specification

  

Operating and Electrical	
Input Voltage	- V
Line Frequency	- Hz
Protection class IEC	-

  

Mechanical and Housing	
Overall length	630 mm
Overall width	630 mm
Overall height	145 mm
Dimensions (height x width x depth)	145 x 630 x 630 mm

Material	Steel
Ingress protection code	-
Mech. impact protection code	-
Accessory colour	White
Angle	-
Net Weight (Piece)	5.500 kg

  

Approval and Application	
CE mark	Yes
EU RoHS compliant	Yes

  

Product Data	
Order product name	CR350Z SMB W60L60

## Cleanroom CR350B

Full product name	CR350Z SMB W60L60
Full EOC	871869979753900
Order code	912401483401
Material no. (12 NC)	912401483401
Numerator – quantity per pack	1

EAN/UPC – Product/Case	8718699797539
Numerator – packs per outer box	1
EAN/UPC – Case	8718699797539

### Dimensional drawing

