



Cleanroom CR350B

CR350Z SMB W30L120

Cleanroom CR350B, Accessory, Steel, White

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

Product data

General Information			
Value ladder	Specification	Material	Steel
		Ingress protection code	-
		Mech. impact protection code	-
		Accessory colour	White
		Angle	-
		Net Weight (Piece)	5.800 kg
Operating and Electrical		Approval and Application	
Input Voltage	- V	CE mark	Yes
Line Frequency	- Hz	EU RoHS compliant	Yes
Protection class IEC	-		
Mechanical and Housing		Product Data	
Overall length	1,230 mm	Order product name	CR350Z SMB W30L120
Overall width	330 mm		
Overall height	155 mm		
Dimensions (height x width x depth)	155 x 330 x 1230 mm		

Cleanroom CR350B

Full product name	CR350Z SMB W30L120
Full EOC	871869979754600
Order code	912401483402
Material no. (12 NC)	912401483402
Numerator – quantity per pack	1

EAN/UPC – Product/Case	8718699797546
Numerator – packs per outer box	1
EAN/UPC – Case	8718699797546

Dimensional drawing

