



Cleanroom CR350B

CR350Z SMB W30L120

Cleanroom CR350B, Accessory, Steel, White

When operating a highly hygienic facility, the demands placed on light are very high and it must comply with strict standards; it must be easy to clean, dust-free, sealed and waterproof – all while offering exceptional optical performance. Philips CR350B Cleanroom luminaires are designed specifically for facilities where hygiene is critical, such as hospitals, laboratories, surgical and examination rooms, as well as applications in the pharmaceutical industry. These energy-efficient, durable cleanroom lighting solutions deliver excellent quality of light that complies with the strictest norms, as well as legislation that requires special IP65, easy-to-clean, dust-free luminaires. Thanks to excellent quality of light and colour rendering, Cleanroom luminaires also reduce eye strain. This can make all the difference in industries such as cleanroom production, graphics and textile manufacturing where high lumen and low glare light are so important.

Product data

General Information		Material	
Value ladder	Specification	Material	Steel
Operating and Electrical		Ingress protection code	-
Input Voltage	- V	Mech. impact protection code	-
Line Frequency	- Hz	Accessory colour	White
Protection class IEC	-	Angle	-
Mechanical and Housing		Net Weight (Piece)	5.800 kg
Overall length	1,230 mm	Approval and Application	
Overall width	330 mm	CE mark	Yes
Overall height	155 mm	EU RoHS compliant	Yes
Dimensions (height x width x depth)	155 x 330 x 1230 mm	Product Data	
		Order product name	CR350Z SMB W30L120

Cleanroom CR350B

Full product name	CR350Z SMB W30L120
Full EOC	871869979754600
Order code	912401483402
Material no. (12 NC)	912401483402
Numerator – quantity per pack	1

EAN/UPC – Product/Case	8718699797546
Numerator – packs per outer box	1
EAN/UPC – Case	8718699797546

Dimensional drawing

