



# Emergency Surface Mounted Downlight

## EM152C SM 2S OA/CO NM3 ELP WH IP65

Emergency Surface Mounted Downlight, Surface mounted emergency downlight, 2 W, 2 W, D155mm; H46 mm, 273 lm, 6500 K, IP65, ELP3h

Safety is important for building owners, and therefore having proper emergency lighting in place is a major concern for them. The Emergency surface mounted Downlight EM152C offers an easy solution for stand-alone emergency lighting, that is fully compliant with European regulations. The lithium battery (LiFePO4) has many advantages over nickel-based products, as it has a longer lifetime, better discharge behavior, is produced in a more welfare friendly way and can be recycled. Two interchangeable lenses are supplied with the product, to adjust the beam angle to the application.

### Product data

General Information	
Lamp family code	-
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Mounting	Surface
Value ladder	Value
Serviceability class	Class C, luminaire without serviceable parts, not serviceable
Warranty period	5 years

Sustainability rating	Unclassified
Light Technical	
Upward light output ratio	0.0
Luminous Flux	273 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	135 lm/W
Color rendering index (CRI)	>80
Light source color	6500
Optic type	Open area or corridor optic
Luminaire light beam spread	150° - 80° x 30°

# Emergency Surface Mounted Downlight

Optic type outdoor	-
Effective projected area	25 m <sup>2</sup>

## Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 Hz
Initial CLO power consumption	2 W
Average CLO power consumption	2 W
End CLO power consumption	2 W
Inrush current	3.04 A
Inrush time	100 ms
Power Consumption	2 W
Power Factor (Fraction)	0.39
Connection	2 Push-in connector 3-pole
Cable	-
Number of products on MCB of 16 A type B	213
Suitable for random switching	Not applicable
Protection class IEC	Safety class II

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Control interface	Internal (no external connection)
Constant light output	No
Maximum dim level	Not applicable
Embedded control	-

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover material	UV stabilized Polycarbonate cover
Fixation material	-
Housing Color	White
Mounting device	-
Optical cover finish	Clear
Reflector Finish	-
Overall height	46 mm
Overall diameter	155 mm
Parts color	All parts colored
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK03 [0.3 J]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Optical cover type	-
Net Weight (Piece)	0.415 kg

## Emergency Operation

Emergency flux	273 lm
Rated duration of the emergency lighting (when fully charged)	3 hour(s)

Additional max. power consumption when emergency battery is charging	2 W
Central Emergency	No
Emergency lighting	Emergency lighting 3 hours duration Pro version
Emergency function testing method	Automatic pre-programmed self testing
Emergency lighting operation mode	Non-maintained

## Approval and Application

Glow-wire test	-
Flammability mark	-
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	25 °C
Ambient temperature range	+5 to +40 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	0.33
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 35000 h	5 %
Control gear failure rate at median useful life 50000 h	10 %
Control gear failure rate at median useful life 75000 h	25 %
Control gear failure rate at median useful life 100000 h	50 %
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 35000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 50000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 75000 h	L95
Lumen maintenance (EN-IEC 62722-2-1) at median useful life* 100000 h	L95

## Product Data

Order product name	EM152C SM 2S OA/CO NM3 ELP WH IP65
Full product name	EM152C SM 2S OA/CO NM3 ELP WH IP65
Full product code	871869979892500
Order code	912401483507

# Emergency Surface Mounted Downlight

Material Nr. (12NC)	912401483507	EAN/UPC - Case	8718699799908
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718699798925		
Numerator - Packs per outer box	20		

## Dimensional drawing

