



PrimaVision Power for CDM

HID-PV C 150 /S CDM 220-240V 50/60Hz


PrimaVision Power gear is designed for optimal performance of 100 and 150 W CDM lamps – ideal where high-intensity light is key.

Product data

Operating and Electrical		Net Weight (Piece)	
Input Voltage	220 to 240 V		0.360 kg
Line Frequency	50 to 60 Hz	Approval and Application	
Input Frequency	50 to 60 Hz	Approval Marks	F-Marking CE marking VDE certificate VDE-EMV certificate CB Certificate
Earth Leakage Current (Max)	0.35 mA	Ambient temperature range	-20 °C to 60 °C
Inrush Current Width	.50 ms	Product Data	
Inrush Current Peak (Max)	50 A	Order product name	HID-PV C 150 /S CDM 220-240V 50/60Hz
Number of Products on MCB (16A Type B) (Nom)	6	Full product name	HID-PV C 150 /S CDM 220-240V 50/60Hz
Wiring		Full product code	871150091052330
Cable Length From Device to Lamp	2.0 m	Order code	913700614066
Connector Type	Insert	Material Nr. (12NC)	913700614066
Temperature		Local order code	HIDPVC150SCDM
T-Case Lifetime (Nom)	75 °C	Numerator - Quantity Per Pack	1
T-Case Maximum (Max)	85 °C	EAN/UPC - Product/Case	8711500910523
Mechanical and Housing		Numerator - Packs per outer box	12
Housing	/S	EAN/UPC - Case	8711500910530

PrimaVision Power for CDM

Dimensional drawing



Product	D1	C1	A1	A2	B1	B2
HID-PV C 150 /S CDM 220-240V 50/60Hz	4.8 mm	32.0 mm	135.0 mm	123.5 mm	75.0 mm	63.5 mm

