



EB-T Electronic ballasts for TL5 lamps (India)

EBT 228 TL5 240

Slim, lightweight, high-frequency electronic ballasts for TL5 lamps

Product data


Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Inrush Current Width	250 ms
Inrush Current Peak (Max)	24 A
Number of Products on MCB (16A Type B) (Nom)	28
Wiring	
Connector Type Input Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Connector Type Output Terminals	WAGO 251 universal connector [Suitable for both automatic wiring (ALF and ADS) and manual wiring]
Temperature	
T-Case Maximum (Max)	75 °C
Mechanical and Housing	
Net Weight (Piece)	0.210 kg

Approval and Application	
Energy Efficiency Index	A3
Safety Standard	IEC 61347-2-3
Approval Marks	CE marking S Mark
Ambient temperature range	0 °C to 50 °C

Product Data	
Order product name	EBT 228 TL5 240
Full product name	EBT 228 TL5 240
Full product code	872790091032200
Order code	913702249232
Material Nr. (12NC)	913702249232
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500999566
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900910322

EB-T Electronic ballasts for TL5 lamps (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
EBT 228 TL5 240	4.2 mm	29.0 mm	258.0 mm	244.0 mm	30.0 mm

