

HID-Basic Gearbox system for SON (India)

BSN 150 X261

Impregnated electromagnetic ballasts of copper and steel construction for use in combination with an external ignitor for High-Pressure Sodium Vapor (SON) lamps

Warnings and Safety

- Ballasts are only suitable for use with integrated luminaires

Product data

Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Input Frequency	50 Hz

Wiring	
Connector Type	Screw


Mechanical and Housing	
Net Weight (Piece)	2.055 kg

Approval and Application	
Energy Efficiency Index	Not specified
Approval Marks	CE marking

Product Data	
Order product name	BSN 150 X261
Full product name	BSN 150 X261
Full product code	871150088460200
Order code	913702253212
Material Nr. (12NC)	913702253212
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500884602
Numerator - Packs per outer box	4
EAN/UPC - Case	8727900067583

HID-Basic Gearbox system for SON (India)

Dimensional drawing



Product	D1	C1	A1	A2	B1
BSN 150 X261	6.3 mm	64.0 mm	132.0 mm	116.0 mm	75.0 mm

