



Dynalite Sensors

DUS90WHB-D

The Philips Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

Mechanical and Housing		Full product name	
Net Weight (Piece)	75.000 g	DUS90WHB-D	
Approval and Application		Full product code	
CE mark	Yes	871869600511800	
EU RoHS compliant	Yes	Order code	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	913703015509	
Ambient temperature range		Material Nr. (12NC)	
-5 to +50 °C		913703015509	
Product Data		Numerator - Quantity Per Pack	
Order product name	DUS90WHB-D	1	
		EAN/UPC - Product/Case	
		8718696005118	
		Numerator - Packs per outer box	
		1	
		EAN/UPC - Case	
		8718696012611	

Dynalite Sensors

Dimensional drawing

