



Dynalite Sensors

DUS360CS

The Dynalite sensor range combines motion detection, light level detection and IR receive in one unit. Each of these features can be operated at the same time, allowing automation scenarios such as turning on the lights after detecting motion and then dimming the lighting level once the available sunlight has been measured, thereby providing additional energy savings. By combining each of these functions into one device, operational efficiency is improved. Each sensor has an in-built microprocessor, allowing logical functions to control one small room, the floor of a building, or an entire building. All sensors receive their power from the DyNet network, and as they are fully remotely programmable, they can be configured to automate and control a virtually unlimited number of controlled outputs.

Product data

Mechanical and Housing		Full product name	
Net Weight (Piece)	0.220 kg	DUS360CS	
Approval and Application		Full product code	
CE mark	Yes	871869688796700	
EU RoHS compliant	Yes	Order code	
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	913703243109	
Product Data		Material Nr. (12NC)	
Ambient temperature range	0 to +45 °C	913703243109	
Order product name	DUS360CS	Numerator - Quantity Per Pack	
		1	
		EAN/UPC - Product/Case	
		8718696887967	
		Numerator - Packs per outer box	
		1	
		EAN/UPC - Case	
		8718696894965	