



# Electronic semi-parallel ignitor for HID lamp circuits

## SN 58

HID ignitors for semi-parallel systems


### Product data

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Operating and Electrical</b> |                             |
| Input Voltage                   | 220 to 240 V                |
| Line Frequency                  | 50 to 60 Hz                 |
| Input Frequency                 | 50 to 60 Hz                 |
| <b>Wiring</b>                   |                             |
| Connector Type                  | Screw                       |
| <b>Temperature</b>              |                             |
| T-Case Maximum (Max)            | 90 °C                       |
| <b>Mechanical and Housing</b>   |                             |
| Housing                         | Akulon S223                 |
| Net Weight (Piece)              | 0.049 kg                    |
| <b>Approval and Application</b> |                             |
| Approval Marks                  | CE marking ENEC certificate |

|                                 |                 |
|---------------------------------|-----------------|
| Ambient temperature range       | -20 °C to 85 °C |
| <b>Product Data</b>             |                 |
| Order product name              | SN 58           |
| Full product name               | SN 58           |
| Full product code               | 697013372881900 |
| Order code                      | 913710010513    |
| Material Nr. (12NC)             | 913710010513    |
| Numerator - Quantity Per Pack   | 1               |
| EAN/UPC - Product/Case          | 6970133728819   |
| Numerator - Packs per outer box | 48              |
| EAN/UPC - Case                  | 6970133728826   |

# Electronic semi-parallel ignitor for HID lamp circuits

## Dimensional drawing



| Product | C1      | A1      | A2      | B1      |
|---------|---------|---------|---------|---------|
| SN 58   | 38.5 mm | 85.5 mm | 65.0 mm | 41.5 mm |

