



# RoadForce

## BRP482 LED186-2S NW 110W DML P7 0-10

110 W, Grey

With an extremely high measured efficacy of up to 190 lm/W, excellent optical gear and great installation flexibility with an integrated angle adjustment system, the RoadForce family ensures a high-quality luminous result compliant with local application standards. Designed with robust components, the RoadForce luminaire complies with the highest quality standards while reducing the maintenance costs.

### Warnings and Safety

- Follow the mounting instructions provided by the manufacturer.

### Product data

General Information	
Lamp family code	-
Light source replaceable	Yes
Driver included	Yes
Light Technical	
Luminous Flux	18,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	169 lm/W
Color rendering index (CRI)	70
Luminaire light beam spread	-
Effective projected area	0.04 m <sup>2</sup>
Operating and Electrical	
Input Voltage	120 to 277 V
Line Frequency	50 or 60 Hz
Inrush current	75.6 A

Inrush time	0.858 ms
Power Consumption	110 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	-
Number of products on MCB of 16 A type B	3
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 10 kV
Controls and Dimming	
Dimmable	0-10V
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminium pressure die cast

## RoadForce

Housing Color	Grey
Mounting device	Mounting bracket adjustable
Overall height	126 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Standard tilt angle posttop	-
Standard tilt angle side entry	0°
Net Weight (Piece)	3.650 kg

### Approval and Application

Ambient temperature range	-20 to +50 °C
---------------------------	---------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

### Over Time Performance (IEC Compliant)

Median useful life L70B50	102,000 hour(s)
---------------------------	-----------------

### Product Data

Order product name	BRP482 LED186-2S NW 110W DML P7 0-10
Full product name	BRP482 LED186-2S NW 110W DML P7 0-10
Order code	919306034951
Material Nr. (12NC)	919306034951
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

