



EssentialForce Plus

BRP231 LED140 NW 87W DML P7 0-10

LED140 | LED module 14000 lm, 87 W, Gray

With a measured efficacy of up to 165 lm/W, great optical performance and robustness, EssentialForce Plus ensures great return on investment and compliance to application standards.

Warnings and Safety

- Follow the mounting instructions provided by the manufacturer.

Product data

General Information	
Lamp family code	LED140 [LED module 14000 lm]
Light source replaceable	Yes
Driver included	Yes
Value ladder	Value
Light Technical	
Luminous Flux	14,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	161 lm/W
Color rendering index (CRI)	70
Luminaire light beam spread	15° x 88°
Effective projected area	0.0276 m ²
Operating and Electrical	
Input Voltage	120 to 277 V
Line Frequency	50 or 60 Hz
Average CLO power consumption	87 W
Inrush current	70 A

Inrush time	160 ms
Power Consumption	87 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable without plug 3-pole
Number of products on MCB of 16 A type B 22	
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 10 kV
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating
Control interface	Analog
Constant light output	No
Maximum dim level	1%
Mechanical and Housing	
Housing Material	Aluminum
Housing Color	Gray

EssentialForce Plus

Mounting device	Spigot
Overall length	304 mm
Overall width	277 mm
Overall height	135 mm
Overall diameter	60 mm
Dimensions (Height x Width x Depth)	135 x 277 x 304 mm
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°+5°-5°
Net Weight (Piece)	2.600 kg

Approval and Application

Ambient temperature range	-5 to +50 °C
---------------------------	--------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
-------------------------	-------

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Median useful life L70B50	102,000 hour(s)
---------------------------	-----------------

Product Data

Order product name	BRP231 LED140 NW 87W DML P7 0-10
Full product name	BRP231 LED140 NW 87W DML P7 0-10
Order code	919306038121
Material Nr. (12NC)	919306038121
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

