



LED Emergency Lighting

Lum Emergencia LEDR1W5

LED Emergency Lighting, 2 W, 220 lm, 6500 K

The Philips LED Emergency luminaire is an economical line of emergency lighting units that provide a solution for commercial and retail applications with a price sensitive budget without compromising on quality and appearance.

Warnings and Safety

- Product for indoor use
- Make sure that the ground wire is connected correctly
- The luminaire heats up during operation. We recommend first switching it off and waiting until it cools down again

Product data

General Information		Inrush time	
Light source replaceable	No		0.5 ms
Driver included	Yes	Power Consumption	2 W
		Power Factor (Fraction)	0.9
		Connection	Flying leads/wires
		Cable	-
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	220 lm	Dimmable	No
Correlated Color Temperature (Nom)	6500 K	Driver/power unit/transformer	Power supply unit (On/Off)
Luminous Efficacy (rated) (Nom)	100 lm/W	Constant light output	No
Color rendering index (CRI)	-		
Operating and Electrical		Mechanical and Housing	
Input Voltage	120 to 277 V	Housing Material	Acrylonitrile butadiene styrene
Line Frequency	60 Hz		
Inrush current	1 A		

LED Emergency Lighting

Housing Color	White
Overall height	110 mm
Ingress protection code	IP20 [Finger-protected]
Net Weight (Piece)	0.500 kg

Approval and Application

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	30,000 hour(s)
---------------------------	----------------

Product Data

Order product name	Lum Emergencia LEDR1W5
Full product name	Lum Emergencia LEDR1W5
Order code	919406020731
Material Nr. (12NC)	919406020731
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699521677
Numerator - Packs per outer box	6
EAN/UPC - Case	8718699521684

