



# Greenbay BY400V

## BY400V LED110S CW SY60 PSU S2 PC WH

GreenBay is an integrally designed, versatile lighting solution from Philips to address lighting application requirements within industrial spaces. From under canopies to truss mounted medium bay luminaires, GreenBay can be used in variety of recessed, surface or suspended mounted applications.

### Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	3 years
Light Technical	
Luminous Flux	11,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	>70
Beam angle of light source	60 degree(s)
Light source color	756 cool white
Optic type	Symmetrical
Luminaire light beam spread	60°
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Power Consumption	110 W
Power Factor (Fraction)	0.9
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 4 kV

Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optic material	Glass
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Via U Shaped Bracket, Aiming Scale Angle, Universal Installation
Overall length	475 mm
Overall width	365 mm
Overall height	165 mm
Dimensions (Height x Width x Depth)	165 x 365 x 475 mm
Material	Aluminum
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Optical cover type	Glass
Net Weight (Piece)	7.800 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

# Greenbay BY400V

<b>Ambient temperature range</b>	0 to +45 °C
<b>Initial Performance (IEC Compliant)</b>	
<b>Power consumption tolerance</b>	+/-10%
<b>Over Time Performance (IEC Compliant)</b>	
<b>Median useful life L70B50</b>	50,000 hour(s)
<b>Product Data</b>	
<b>Order product name</b>	BY400V LED110S CW SY60 PSU S2 PC WH

<b>Full product name</b>	BY400V LED110S CW SY60 PSU S2 PC WH
<b>Order code</b>	919515810965
<b>Material Nr. (12NC)</b>	919515810965
<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	1

## Dimensional drawing

Product: GreenBay  
 Type: BY400V  
 Application: Indoor

