



DaySpace

RC740B LED25S/840 W60L60 WH

For the modern workspace lighting challenges that may inspire exciting new concepts or rejuvenate routine patterns, DaySpace offers a distinctive approach with the emphasis on the overall integrated look of the ceiling rather than on the luminaire itself. DaySpace discreetly integrates into the ceiling to deliver soft and ethereal yet brilliant environments. A luminous web or well-defined squares perched for a geometric yet whimsical space – DaySpace comes to your design rescue. For the Architects, Designers & Real Estate Professionals Designing/ Developing Next Gen Office Spaces DaySpace Provides. Creative Freedom to Blend in Lighting as an Architectural Element of the office. The opportunity to create the desired ambience through its customizable nature. To Declutter and break away from the Boring 2'x2' Lighting. Because of its unique design that minimizes the intrusion of the lighting surface into the office architecture and create a completely customized ambience

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

Product data

| General Information | |
|------------------------------------|-------------------|
| Driver included | Yes |
| Light source engine type | LED |
| Warranty period | 3 years |
| Light Technical | |
| Luminous Flux | 2,800 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 90 lm/W |
| Color rendering index (CRI) | >80 |
| Beam angle of light source | 120 degree(s) |
| Light source color | 840 neutral white |

| Optic type | Beam angle 120° |
|--|-------------------------------------|
| Luminaire light beam spread | 120° |
| Operating and Electrical | |
| Input Voltage | 120 to 277 V |
| Line Frequency | 50 Hz |
| Power Consumption | 30 W |
| Power Factor (Fraction) | 0.9 |
| Protection class IEC | Safety class I |
| Surge Protection (Common/Differential) | Surge protection level until 2.5 kV |

Controls and Dimming

| | |
|-------------------|----|
| Dimmable | No |
| Control interface | - |

Mechanical and Housing

| | |
|------------------------------|-----------------------------------|
| Housing Material | Steel |
| Optic material | Polycarbonate |
| Optical cover material | Polystyrene |
| Housing Color | White RAL9016 |
| Mounting device | Recessed mounting box square |
| Material | Steel |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Optical cover type | UV stabilized Polycarbonate cover |
| Net Weight (Piece) | 3.500 kg |

Approval and Application

| | |
|-------------------|---|
| Flammability mark | For mounting on normally flammable surfaces |
|-------------------|---|

| | |
|---------------------------|-------------|
| Ambient temperature range | 0 to +45 °C |
|---------------------------|-------------|

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|


Over Time Performance (IEC Compliant)

| | |
|---------------------------|----------------|
| Median useful life L70B50 | 50,000 hour(s) |
|---------------------------|----------------|

Product Data

| | |
|---------------------------------|-----------------------------|
| Order product name | RC740B LED25S/840 W60L60 WH |
| Full product name | RC740B LED25S/840 W60L60 WH |
| Order code | 919515812989 |
| Material Nr. (12NC) | 919515812989 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 2 |

Dimensional drawing



Note - Actual product may differ from pictorial view.

