

DaySpace

SP740B LED30S/840 W60L60 PSU WH

For the modern workspace lighting challenges that may inspire exciting new concepts or rejuvenate routine patterns, DaySpace offers a distinctive approach with the emphasis on the overall integrated look of the ceiling rather than on the luminaire itself. DaySpace discreetly integrates into the ceiling to deliver soft and ethereal yet brilliant environments. A luminous web or well-defined squares perched for a geometric yet whimsical space – DaySpace comes to your design rescue. For the Architects, Designers & Real Estate Professionals Designing/ Developing Next Gen Office Spaces DaySpace Provides. Creative Freedom to Blend in Lighting as an Architectural Element of the office. The opportunity to create the desired ambience through its customizable nature. To Declutter and break away from the Boring 2'x2' Lighting. Because of its unique design that minimizes the intrusion of the lighting surface into the office architecture and create a completely customized ambience

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.


Product data

General Information		Optic type		Beam angle 120°
Driver included	Yes	Luminaire light beam spread		120°
Light source engine type	LED			
Warranty period	3 years			
Light Technical		Operating and Electrical		
Luminous Flux	3,300 lm	Input Voltage	120 to 277 V	
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 Hz	
Luminous Efficacy (rated) (Nom)	90 lm/W	Power Consumption	37 W	
Color rendering index (CRI)	>80	Power Factor (Fraction)	0.9	
Beam angle of light source	120 degree(s)	Protection class IEC	Safety class I	
Light source color	840 neutral white	Surge Protection (Common/Differential)	Surge protection level until 2.5 kV	

Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Steel
Optic material	Polycarbonate
Optical cover material	Polystyrene
Housing Color	White RAL9016
Mounting device	Recessed mounting box square
Material	Steel
Ingress protection code	IP20 (Finger-protected)
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	UV stabilized Polycarbonate cover
Net Weight (Piece)	6.000 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

Ambient temperature range	0 to +45 °C
Initial Performance (IEC Compliant)	
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Product Data	
Order product name	SP740B LED30S/840 W60L60 PSU WH
Full product name	SP740B LED30S/840 W60L60 PSU WH
Order code	919515813689
Material Nr. (12NC)	919515813689
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



Note - Actual product may differ from pictorial view.

