

DaySpace

SP740B LED36S/840 W60L60 PSU WH

For the modern workspace lighting challenges that may inspire exciting new concepts or rejuvenate routine patterns, DaySpace offers a distinctive approach with the emphasis on the overall integrated look of the ceiling rather than on the luminaire itself. DaySpace discreetly integrates into the ceiling to deliver soft and ethereal yet brilliant environments. A luminous web or well-defined squares perched for a geometric yet whimsical space – DaySpace comes to your design rescue. For the Architects, Designers & Real Estate Professionals Designing/ Developing Next Gen Office Spaces DaySpace Provides. Creative Freedom to Blend in Lighting as an Architectural Element of the office. The opportunity to create the desired ambience through its customizable nature. To Declutter and break away from the Boring 2'x2' Lighting. Because of its unique design that minimizes the intrusion of the lighting surface into the office architecture and create a completely customized ambience

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

Product data

General Information		Optic type	
Driver included	Yes	Beam angle 120°	
Light source engine type	LED	Luminaire light beam spread	
Warranty period	3 years	120°	
Light Technical		Operating and Electrical	
Luminous Flux	3,800 lm	Input Voltage	120 to 277 V
Correlated Color Temperature (Nom)	4000 K	Line Frequency	50 Hz
Luminous Efficacy (rated) (Nom)	90 lm/W	Power Consumption	44 W
Color rendering index (CRI)	>80	Power Factor (Fraction)	0.9
Beam angle of light source	120 degree(s)	Protection class IEC	Safety class I
Light source color	840 neutral white	Surge Protection (Common/Differential)	Surge protection level until 2.5 kV

Controls and Dimming

Dimmable	No
Control interface	-

Mechanical and Housing

Housing Material	Steel
Optic material	Polycarbonate
Optical cover material	Polystyrene
Housing Color	White RAL9016
Mounting device	Recessed mounting box square
Material	Steel
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	UV stabilized Polycarbonate cover
Net Weight (Piece)	6.000 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
-------------------	---

Ambient temperature range	0 to +45 °C
---------------------------	-------------

Initial Performance (IEC Compliant)

Power consumption tolerance	+/-10%
-----------------------------	--------


Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	SP740B LED36S/840 W60L60 PSU WH
Full product name	SP740B LED36S/840 W60L60 PSU WH
Order code	919515813692
Material Nr. (12NC)	919515813692
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



Note - Actual product may differ from pictorial view.

