



SunStay

BRP710 LED30 WW MR HY SOLAR

Integrated solar street light with Lithium Ferro Phosphate battery, solar panel and charger built into the luminaire. Pressure die cast aluminium for sturdiness and long life. Specially designed pole mounting bracket allows different tilt angles, lateral and pole top mounting.

Product data

General Information	
Driver included	Yes
Value ladder	Specification
Warranty period	3 years
Light Technical	
Luminous Flux	3,000 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	175 lm/W
Color rendering index (CRI)	>70
Operating and Electrical	
Input Voltage	240 V
Line Frequency	50 Hz
Battery type	Lithium Ferro Phosphate
Battery ampere hour	20 Ah
Battery voltage	12.8 V
Battery charging & discharging cycles	2000
Panel type	Mono crystalline
Panel voltage	17 Vmp, 21 Voc V
Panel peak wattage	35 W
Charge controller type	MPPT
Charge controller wattage	17 W

Cable connection kit	Included
Cable	Cable 0.8m, 2-core, 1.5mm2
Grid connection type	Hybrid
Surge Protection (Common/Differential)	Surge protection level until 4 kV

Controls and Dimming	
Dimmable	Yes
Configurability	Factory Configurable
Solar dimming profile	100% Dusk to dawn

Mechanical and Housing	
Housing Color	RAL 7011
Overall length	684 mm
Overall width	369 mm
Overall height	156 mm
Dimensions (Height x Width x Depth)	156 x 369 x 684 mm
Material	Pressure die cast aluminum
Battery location	Inside Luminaire
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	UV stabilized Polycarbonate cover

SunStay

Net Weight (Piece)	12.000 kg
--------------------	-----------

Approval and Application

CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	0 to +35 °C

Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Application Conditions

Ambient temperature range for charging	0 °C to +45 °C
Ambient temperature range for discharging (when light is on)	-20 °C to +35 °C

Product Data

Order product name	BRP710 LED30 WW MR HY SOLAR
Full product name	BRP710 LED30 WW MR HY SOLAR
Full product code	871951450201700
Order code	919515813995
Material Nr. (12NC)	919515813995
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514502017
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514502017

Dimensional drawing

