



Greenperform Prime Gen2

BY617P LED300S 5700 ENB PSU GR

In an age where sustainability, high performance/productivity standards and building unique identities are the top priorities for businesses, GreenPerform Prime gen2 provides an unmatched highbay solution for a wide range of applications like warehousing, manufacturing, other industrial applications, atriums, airport concourse, sports halls, etc. GreenPerform Prime Gen2 not only guarantees assured performance but also fits stylishly into diverse design plans. Apart from the unique look and feel, it offers best in class system efficacy, superior light quality, multiple beam angles, and glare control to provide the users with nothing less than the best in the industry

Warnings and Safety

- Meant for use in Indoor Industrial environment only.

Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	1 years
Light Technical	
Luminous Flux	30,000 lm
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	160 lm/W
Color rendering index (CRI)	≥70
Beam angle of light source	30 degree(s)
Light source color	757 cool white
Optic type	-

Luminaire light beam spread	30°
Operating and Electrical	
Input Voltage	120 to 277 V
Line Frequency	50 Hz
Power Consumption	190 W
Power Factor (Fraction)	0.95
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	6/6 kV
Controls and Dimming	
Dimmable	No

Greenperform Prime Gen2

Control interface	-
Mechanical and Housing	
Housing Material	Aluminium pressure die cast
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Aluminum and gray
Mounting device	Eye-Bolt
Optical cover shape	-
Overall height	196 mm
Overall diameter	421 mm
Material	Pressure die cast aluminum
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Optical cover type	Micro-lens optic in polycarbonate cover
Net Weight (Piece)	4.700 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

Ambient temperature range	0 to +45 °C
Initial Performance (IEC Compliant)	
Initial chromaticity	<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	50,000 hour(s)
Product Data	
Order product name	BY617P LED300S 5700 ENB PSU GR
Full product name	BY617P LED300S 5700 ENB PSU GR
Order code	919515815503
Material Nr. (12NC)	919515815503
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing

Dimensions in mm

