



# Pureline slim

## SP780X H LED20S-4000 PSU W5L112 OC S1 WH

The PureLine Slim family of luminaires gives you compromise-free office illumination. It is a perfect solution for office application and general indoor area lighting with Sleek profile which helps Declutter the ceilings. The range brings together high-flux lighting with a homogeneous optical system without making any concessions on energy efficiency design.

### Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

### Product data

General Information	
Driver included	Yes
Light source engine type	LED
Warranty period	1 years

Light Technical	
Luminous Flux	2,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color rendering index (CRI)	80
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	-
Luminaire light beam spread	-

Operating and Electrical	
Input Voltage	140-270 V
Line Frequency	50 Hz
Power Consumption	20 W

Power Factor (Fraction)	0.9
Protection class IEC	Safety class I
Surge Protection (Common/Differential)	Surge protection level until 4 kV

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum extruded
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White RAL9016
Mounting device	Suspension set simple, standard
Optical cover shape	-
Overall length	1,126 mm
Overall width	53 mm
Overall height	70 mm
Dimensions (Height x Width x Depth)	70 x 53 x 1126 mm

## Pureline slim

<b>Material</b>	Aluminum
<b>Ingress protection code</b>	IP20 [Finger-protected]
<b>Mech. impact protection code</b>	IK02 [0.2 J standard]
<b>Optical cover type</b>	Polycarbonate bowl/cover prismatic
<b>Net Weight (Piece)</b>	1.800 kg

### Approval and Application

<b>Flammability mark</b>	For mounting on normally flammable surfaces
<b>Ambient temperature range</b>	0 to +45 °C

### Initial Performance (IEC Compliant)

<b>Initial chromaticity</b>	<5
<b>Power consumption tolerance</b>	+/-10%

### Over Time Performance (IEC Compliant)

<b>Median useful life L70B50</b>	50,000 hour(s)
----------------------------------	----------------

### Product Data

<b>Order product name</b>	SP780X H LED20S-4000 PSU W5L112 OC S1 WH
<b>Full product name</b>	SP780X H LED20S-4000 PSU W5L112 OC S1 WH
<b>Order code</b>	919515815914
<b>Material Nr. (12NC)</b>	919515815914
<b>Numerator - Quantity Per Pack</b>	1
<b>Numerator - Packs per outer box</b>	4

