



Glazeline

SP790P | LED26S 840 PSU W6L120 OD WH

The GlazeLine Slim family of luminaires gives you compromise-free office illumination with deep recessed optics to reduce the glare and increase the employee productivity. It is a perfect solution for office application and general indoor area lighting with Sleek profile which helps Declutter the ceilings. The range brings together flexible color options with specialized optics without making any concessions on energy efficiency design.

Warnings and Safety

- Meant for Indoor Application Only. Should not be used in outdoor environment.

Product data

General Information		Operating and Electrical	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 Hz
Warranty period	1 years	Power Consumption	22 W
		Power Factor (Fraction)	0.9
		Protection class IEC	Safety class I
		Surge Protection (Common/Differential)	4/4 kV kV
Light Technical		Controls and Dimming	
Luminous Flux	2,600 lm	Dimmable	-
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	118 lm/W		
Color rendering index (CRI)	80	Mechanical and Housing	
Beam angle of light source	- degree(s)	Housing Material	Aluminum extruded
Light source color	840 neutral white	Optic material	Polycarbonate
Optic type	-	Optical cover material	Polycarbonate
Luminaire light beam spread	-	Housing Color	White
Optic type outdoor	-	Mounting device	Suspension set simple, standard
Unified glare rating CEN	Not applicable		

Optical cover shape	Flat
Overall length	1,200 mm
Overall width	65 mm
Overall height	100 mm
Dimensions (Height x Width x Depth)	100 x 65 x 1200 mm
Material	Aluminum
Ingress protection code	IP20 [No protection]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Opal diffuser in polycarbonate cover
Net Weight (Piece)	3.300 kg

Approval and Application

Flammability mark	For mounting on normally flammable surfaces
Ambient temperature range	0 to +45 °C

Initial Performance (IEC Compliant)

Initial chromaticity	<5
----------------------	----

Power consumption tolerance	+/-10%
-----------------------------	--------


Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

Product Data

Order product name	SP790P I LED26S 840 PSU W6L120 OD WH
Full product name	SP790P I LED26S 840 PSU W6L120 OD WH
Order code	919515816742
Material Nr. (12NC)	919515816742
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Dimensional drawing



Type Integrated	Type Non Integrated	Dimensions L x W x H mm	Voltage	Frequency	NC
SP790P I WS650	SP790P N WS650 S	650 x 65 x 100	230 V AC	50Hz	1.5
SP790P I WS650	SP790P N WS650 S	518 x 65 x 100	230 V AC	50Hz	1.5
SP790P I WS110	SP790P N WS110 S	550 x 65 x 100	230 V AC	50Hz	2.2
SP790P I WS650	SP790P N WS650 S	808 x 65 x 100	230 V AC	50Hz	2.2
SP790P I WS1120	SP790P N WS1120 S	1200 x 65 x 100	230 V AC	50Hz	2.5
SP790P I WS1110	SP790P N WS1110 S	1110 x 65 x 100	230 V AC	50Hz	2.5
SP790P I WS1150	SP790P N WS1150 S	1457 x 65 x 100	230 V AC	50Hz	1.6
SP790P I WS1150	SP790P N WS1150 S	1412 x 65 x 100	230 V AC	50Hz	1.6
SP790P I WS1180	SP790P N WS1180 S	1797 x 65 x 100	230 V AC	50Hz	4.4
SP790P I WS1180	SP790P N WS1180 S	1762 x 65 x 100	230 V AC	50Hz	4.4
SP790P I WS1240	SP790P N WS1240 S	2388 x 65 x 100	230 V AC	50Hz	5.8
SP790P I WS1240	SP790P N WS1240 S	2353 x 65 x 100	230 V AC	50Hz	5.8
SP790P I WS1650	SP790P N WS1650 S	651 x 65 x 100	230 V AC	50Hz	1.8
SP790P I WS650	SP790P N WS650 S	558 x 65 x 100	230 V AC	50Hz	1.8
SP790P I WS1120	SP790P N WS1120 S	1200 x 65 x 100	230 V AC	50Hz	1.5
SP790P I WS1110	SP790P N WS1110 S	1110 x 65 x 100	230 V AC	50Hz	2.5
SP790P I WS1240	SP790P N WS1240 S	2388 x 65 x 100	230 V AC	50Hz	7.0
SP790P I WS1240	SP790P N WS1240 S	2353 x 65 x 100	230 V AC	50Hz	7.0

