



Standard Life PS

300M/CL

Standard Life Incandescent, vacuum or gas-filled lamp has a crystal clear bulb and a completely visible filament, so the brightness of the light is not 'softened.' It imparts a sparkling radiance to larger luminaires and wall brackets with textured or satin-etched glass and cut crystal. It is the appropriate lamp for large luminaires with clear glass bowls, mounted indoors or outdoors. It is recommended in all such cases where brilliance and sparkle are more important than the avoidance of glare. These lamps are also used for indirect lighting in closed luminaires.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Lighting Technology	Incandescent


Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	PS25
Net Weight (Piece)	0.055 kg

Product Data	
Order product name	300M/CL
Full product name	300M/CL
Order code	920140736305
Material Nr. (12NC)	920140736305
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	067805012362
Numerator - Packs per outer box	12
EAN/UPC - Case	50067805012367

Standard Life PS

Dimensional drawing



Product

300M/CL

