



Infrared Lamps Industrial Use

R125 IR 275W E27 240V 1CT/6

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.


Product data

General Information	
Cap-Base	E27
Nominal lifetime	5,000 hour(s)
Rated Lifetime (Hours)	5,000 hour(s)
Lighting Technology	Incandescent
Operating and Electrical	
Power Consumption	275 W
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	R125
Net Weight (Piece)	0.100 kg
Product Data	
Order product name	R125 IR 275W E27 240V 1CT/6
Full product name	R125 IR 275W E27 240V 1CT/6
Full product code	871150038344001
Order code	923203345503
Material Nr. (12NC)	923203345503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500383440
Numerator - Packs per outer box	6
EAN/UPC - Case	8718291225508

Infrared Lamps Industrial Use

Dimensional drawing



Product	D	C (max)
R125 IR 275W E27 240V 1CT/6	126.5 mm	179 mm

