



Infrared Lamps Industrial Use

BR125 IR 150W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data


General Information		Bulb Material	
Cap-Base	E27	Bulb Material	Hard Glass
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	BR125
Nominal lifetime	5,000 hour(s)	Net Weight (Piece)	104.000 g
Rated Lifetime (Hours)	5,000 hour(s)	Approval and Application	
Lighting Technology	Incandescent	CE mark	Yes
Operating and Electrical		Product Data	
Power Consumption	150 W	Order product name	BR125 IR 150W E27 230-250V CL 1CT/10
Voltage (Nom)	230-250 V	Full product name	BR125 IR 150W E27 230-250V CL 1CT/10
Controls and Dimming		Full product code	871150057522725
Dimmable	Yes	Order code	923211943801
Mechanical and Housing		Material Nr. (12NC)	923211943801
Bulb Finish	Clear	Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500575227
		Numerator - Packs per outer box	10

Infrared Lamps Industrial Use

EAN/UPC - Case

8727900209303

Dimensional drawing



Product	D	C (max)
BR125 IR 150W E27 230-250V CL 1CT/10	125 mm	173 mm

