



Infrared Lamps Industrial Use

R125 IR 300W E27 230-250V CL 1CT/10


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, but also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General Information		Bulb Material	
Cap-Base	E27	Bulb Material	Hard Glass
Operating Position	UNIVERSAL [Any or Universal (U)]	Bulb Shape	R125
Nominal lifetime	5,000 hour(s)	Net Weight (Piece)	99.200 g
Rated Lifetime (Hours)	5,000 hour(s)	Product Data	
Lighting Technology	Incandescent	Order product name	R125 IR 300W E27 230-250V CL 1CT/10
Operating and Electrical		Full product name	R125 IR 300W E27 230-250V CL 1CT/10
Power Consumption	300 W	Full product code	871150012656625
Voltage (Nom)	230-250 V	Order code	923223043807
Controls and Dimming		Material Nr. (12NC)	923223043807
Dimmable	Yes	Numerator - Quantity Per Pack	1
Mechanical and Housing		EAN/UPC - Product/Case	8711500126566
Bulb Finish	Clear	Numerator - Packs per outer box	10
		EAN/UPC - Case	8711500141088

Infrared Lamps Industrial Use

Dimensional drawing



Product	D	C (max)
R125 IR 300W E27 230-250V CL 1CT/10	125 mm	179 mm

