



# Infrared Lamps Industrial Use

## R125 IR 375W E27 230-250V CL 1CT/10

Philips infrared incandescent reflector lamps are designed to work in the toughest environments, such as farms, bathrooms or kitchens and their nearest surrounding. They have a reinforced construction thanks to the use of hard glass. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. Philips infrared lamps provide direct, draught-free warmth to the animals, and also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

### Product data

General Information	
Cap base	E27
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	5,000 h
Rated Lifetime (Hours)	5,000 h
Lighting Technology	Incandescent

Operating and Electrical	
Power Consumption	375 W
Voltage (nom.)	230-250 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear

Bulb material	Hard Glass
Bulb shape	R125
Net Weight (Piece)	137.100 g


Approval and Application	
CE mark	Yes

Product Data	
Order product name	R125 IR 375W E27 230-250V CL 1CT/10
Full product name	R125 IR 375W E27 230-250V CL 1CT/10
Full EOC	871150012659725
Order code	923223543807
Material no. (12 NC)	923223543807
Local order code	IR375CH
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500126597

## Infrared Lamps Industrial Use

Numerator – packs per outer box	10
EAN/UPC - Case	8711500141118

### Dimensional drawing



Product	D	C (max)
R125 IR 375W E27 230-250V CL 1CT/10	125 mm	183 mm

