



Infrared Lamps Industrial Use

R125 IR 375W E27 230-250V CL 1CT/10

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data


General Information		Approval and Application	
Cap-Base	E27	CE mark	Yes
Operating Position	UNIVERSAL [Any or Universal (U)]	Product Data	
Nominal lifetime	5,000 hour(s)	Order product name	R125 IR 375W E27 230-250V CL 1CT/10
Rated Lifetime (Hours)	5,000 hour(s)	Full product name	R125 IR 375W E27 230-250V CL 1CT/10
Lighting Technology	Incandescent	Full product code	871150012659725
Operating and Electrical		Order code	923223543807
Power Consumption	375 W	Material Nr. (12NC)	923223543807
Voltage (Nom)	230-250 V	Numerator - Quantity Per Pack	1
Controls and Dimming		EAN/UPC - Product/Case	8711500126597
Dimmable	Yes	Numerator - Packs per outer box	10
Mechanical and Housing			
Bulb Finish	Clear		
Bulb Material		Hard Glass	
Bulb Shape		R125	
Net Weight (Piece)		137.100 g	

Infrared Lamps Industrial Use

EAN/UPC - Case

8711500141118

Dimensional drawing



Product	D	C (max)
R125 IR 375W E27 230-250V CL 1CT/10	125 mm	183 mm

