



# Infrared Lamps Industrial Use

## PAR38 IR 175W E27 230V Red 1CT/12

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

### Product data


General Information		Controls and Dimming	
Cap-Base	E27	Dimmable	Yes
Operating Position	H45 [h45]	<b>Mechanical and Housing</b>	
Nominal lifetime	5,000 hour(s)	Bulb Finish	Red
Rated Lifetime (Hours)	5,000 hour(s)	Bulb Material	Hard Glass
Lighting Technology	Incandescent	Bulb Shape	PAR38
<b>Light Technical</b>		Net Weight (Piece)	308.000 g
Color Designation	R	<b>Approval and Application</b>	
<b>Operating and Electrical</b>		CE mark	Yes
Power Consumption	175 W	<b>Product Data</b>	
Voltage (Nom)	230 V	Order product name	PAR38 IR 175W E27 230V Red 1CT/12
		Full product name	PAR38 IR 175W E27 230V Red 1CT/12
		Full product code	871150060053015

## Infrared Lamps Industrial Use

Order code	923801444210
Material Nr. (12NC)	923801444210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500600530

Numerator - Packs per outer box	12
EAN/UPC - Case	8727900207316

### Dimensional drawing



Product	D	C (max)	C1 (max)
PAR38 IR 175W E27 230V Red 1CT/12	121 mm	136 mm	124 mm

