



# Halogen reflector

## DDL 150W 20V 24PK

Philips' halogen reflector lamps offer the ideal no-fuss solution for a wide variety of medical, projection and scientific illumination systems. Their proven reliability makes them ideal for retrofit installations. The burners are precisely aligned for optimal light performance. Dichroic reflectors ensure heat dissipation towards the back of the optical system, which helps the optical system remain within temperature limits. A special blue-filter version blocking out unwanted light above 700 nm is available for dental curing applications. In addition, you get all the proven advantages of halogen technology such as a CRI of 100 – the same as natural sunlight for the best possible color rendering. Halogen lamps also create a comfortable warm white light, and they maintain their high lumen output with almost no lumen reduction throughout their lifetime.


### Product data

General Information		Mechanical and Housing	
Cap-Base	GX5.3	Bulb Material	Quartz-UV Open
Operating Position	S105 [s105]	Reflector Finish	Facetted reflector
Life to 50% Failures (Nom)	500 hour(s)	Bulb Shape	R50
		Net Weight (Piece)	0.026 kg
Light Technical		Approval and Application	
Correlated Color Temperature (Nom)	3150 K	CE mark	Yes
Color rendering index (CRI)	100		
Operating and Electrical		Product Data	
Power Consumption	150 W	Order product name	DDL 150W 20V 24PK
Voltage (Nom)	20 V	Full product name	DDL 150W 20V 24PK
		Full product code	871150041061030
Controls and Dimming		Order code	923921419794
Dimmable	Yes	Material Nr. (12NC)	923921419794
		Numerator - Quantity Per Pack	1

## Halogen reflector

EAN/UPC - Product/Case	8711500410610
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419002

### Dimensional drawing



Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

