



Halogen reflector

DDL 150W 20V 24PK

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

Product data

General Information		Net Weight (Piece)	
Cap-Base	GX5.3		0.026 kg
Operating Position	S105 [s105]	Approval and Application	
Life to 50% Failures (Nom)	500 h	CE mark	Yes
Light Technical		Product Data	
Correlated Color Temperature (Nom)	3150 K	Order product name	DDL 150W 20V 24PK
Color rendering index (CRI)	100	Full product name	DDL 150W 20V 24PK
Operating and Electrical		Full product code	871150041061030
Power Consumption	150 W	Local code description	14501
Voltage (Nom)	20 V	Order code	923921419794
Controls and Dimming		Material Nr. (12NC)	923921419794
Dimmable	Yes	Local order code	14501
Mechanical and Housing		Numerator - Quantity Per Pack	1
Bulb Material	Quartz-UV Open	EAN/UPC - Product/Case	8711500410610
Reflector Finish	Facetted reflector	Numerator - Packs per outer box	24
Bulb Shape	R50	EAN/UPC - Case	8711500419002

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

