



# Halogen reflector

## DDL 150W 20V 24PK

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

### Product data

General Information	
Cap-Base	GX5.3
Operating Position	S105 [s105]
Life to 50% Failures (Nom)	500 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3150 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	20 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Facetted reflector

Bulb Shape	R50
Net Weight (Piece)	0.026 kg
Approval and Application	
CE mark	Yes
Product Data	
Order product name	DDL 150W 20V 24PK
Full product name	DDL 150W 20V 24PK
Full product code	871150041061030
Order code	923921419794
Material Nr. (12NC)	923921419794
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500410610
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500419002

## Halogen reflector

### Dimensional drawing



Product	D (max)	C (max)
DDL 150W 20V 24PK	50.7 mm	44.5 mm

