



# Halogen reflector

## DDL 150W 20V 24PK

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

### Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | GX5.3              |
| Operating Position                 | S105 [s105]        |
| Life to 50% Failures (Nom)         | 500 hour(s)        |
| Light Technical                    |                    |
| Correlated Color Temperature (Nom) | 3150 K             |
| Color rendering index (CRI)        | 100                |
| Operating and Electrical           |                    |
| Power Consumption                  | 150 W              |
| Voltage (Nom)                      | 20 V               |
| Controls and Dimming               |                    |
| Dimmable                           | Yes                |
| Mechanical and Housing             |                    |
| Bulb Material                      | Quartz-UV Open     |
| Reflector Finish                   | Facetted reflector |

| Bulb Shape                      | R50               |
|---------------------------------|-------------------|
| Net Weight (Piece)              | 0.026 kg          |
| Approval and Application        |                   |
| CE mark                         | Yes               |
| Product Data                    |                   |
| Order product name              | DDL 150W 20V 24PK |
| Full product name               | DDL 150W 20V 24PK |
| Full product code               | 871150041061030   |
| Order code                      | 923921419794      |
| Material Nr. (12NC)             | 923921419794      |
| Numerator - Quantity Per Pack   | 1                 |
| EAN/UPC - Product/Case          | 8711500410610     |
| Numerator - Packs per outer box | 24                |
| EAN/UPC - Case                  | 8711500419002     |

## Halogen reflector

### Dimensional drawing



| Product           | D (max) | C (max) |
|-------------------|---------|---------|
| DDL 150W 20V 24PK | 50.7 mm | 44.5 mm |

