



Appliance Refrigerator Tubular

15 W E14 cap Incandescent appliance bulb

Tubular lamp with clear glass bulb

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Luminous Flux	110 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	15.0 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T25
Net Weight (Piece)	12.500 g

Approval and Application	
Energy Consumption kWh/1000 h	15 kWh

Product Data	
Order product name	15 W E14 cap Incandescent appliance bulb
Full product name	15 W E14 cap Incandescent appliance bulb
Full product code	871150025024725
Order code	924197744452
Material Nr. (12NC)	924197744452
Numerator - Quantity Per Pack	2
EAN/UPC - Product/Case	8711500250247
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500259837

Appliance Refrigerator Tubular

Dimensional drawing

Product	D (max)	C (max)
15 W E14 cap Incandescent appliance bulb	25 mm	57 mm

