



# Infrared Lamps Industrial Use

## 125BR40 IR/1 120V 4/1 TP

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, but also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	5,000 hour(s)
Lighting Technology	Incandescent

Light Technical	
Number of light sources	1

Operating and Electrical	
Power Consumption	125 W
Wattage Equivalent	125 W
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	BR40
Net Weight (Piece)	0.340 kg


  

Product Data	
Order product name	125BR40 IR/1 120V 4/1 TP
Full product name	125BR40 IR/1 120V 4/1 TP
Order code	925254936311
Material Nr. (12NC)	925254936311
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677416751
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677416756

## Infrared Lamps Industrial Use

---

### Dimensional drawing



Product	D	C (max)
125BR40 IR/1 120V 4/1 TP	125 mm	174.6 mm

