



# PL-C 4-PIN

## PL-C 13W/827/4P 1CT/5X10BOX

PL-C new shape is an efficient and effective medium wattage fluorescent lamp, used in general downlights for retail, hospitality and office applications. The 2 PIN version is designed for electromagnetic gear and is provided with plug in/pull out lamp base. The 4 PIN version is designed for operation on electronic HF control gear with integrated pre-heat and is provided with a plug-in/pull-out lamp base.

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	G24q-1	Power Consumption	13.4 W
Nominal lifetime	8,000 hour(s)	Lamp Current (Nom)	175 mA
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	Yes
Luminous Flux	900 lm	Mechanical and Housing	
Color Designation	Incandescent White	Bulb Shape	PL-C
Chromaticity Coordinate X (Nom)	463	Net Weight (Piece)	0.040 kg
Chromaticity Coordinate Y (Nom)	420	Approval and Application	
Correlated Color Temperature (Nom)	2700 K	Mercury (Hg) Content (Nom)	1.3
Luminous Efficacy (rated) (Nom)	67 lm/W		
Color rendering index (CRI)	>80		

## PL-C 4-PIN

Product Data	
Order product name	PL-C 13W/827/4P 1CT/5X10BOX
Full product name	PL-C 13W/827/4P 1CT/5X10BOX
Full product code	872016922620300
Order code	927812682701
Material Nr. (12NC)	927812682701

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169226203
Numerator - Packs per outer box	50
EAN/UPC - Case	8720169226227

### Dimensional drawing



Product	D (max)	D1 (max)	A	B
PL-C 13W/827/4P 1CT/5X10BOX	26 mm	26 mm	112.5 mm	129 mm

