



TUV PL-S - Compact solution for residential applications

TUV PL-S lamps are compact UV-C 254 nm lamps. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-S lamps offer almost constant UV output over their complete lifetime. Thanks to the single-ended lamp base, lamp replacement is easy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Plants and/or materials that are exposed to UV-C and/or ozone for a long time may become damaged and/or discolored.

General Information

Cap-Base	2G7
Useful Life (Nom)	9,000 hour(s)

Light Technical

Depreciation at Useful Lifetime	20 %
---------------------------------	------

Operating and Electrical

Power Consumption	8.6 W
Lamp Current (Nom)	0.17 A
Voltage (Nom)	60 V


Mechanical and Housing

Net Weight (Piece)	30.000 g
--------------------	----------

Approval and Application

Mercury (Hg) Content (Nom)	3.0 mg
CE mark	Yes

Dimensional drawing




UV

UV-C Radiation at 100 hr	2.3 W
--------------------------	-------

Product Data

Order product name	TUV PL-S 9W/4P
Full product name	TUV PL-S 9W/4P
Full product code	871150071083380
Order code	927901904007
Material Nr. (12NC)	927901904007
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500710833
Numerator - Packs per outer box	60
EAN/UPC - Case	8711500710864

Photometric data



Spectral Power Distribution Colour - TUV PL-S 9W/4P

