



TUV PL-L

TUV PL-L 55W/4P HF 1CT/25

TUV PL-L lamps are compact UVC (germicidal) lamps used in residential water and air disinfection units. The compact size of the lamp allows for a small system design and design flexibility. TUV PL-L lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy. Thanks to the single-ended lamp base, lamp replacement is easy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

Product data


General Information		Mechanical and Housing	
Cap-Base	2G11	Net Weight (Piece)	134.000 g
Useful Life (Nom)	9,000 h		
Light Technical		Approval and Application	
Depreciation at Useful Lifetime	20 %	Mercury (Hg) Content (Nom)	4.4 mg
		CE mark	Yes
Operating and Electrical		UV	
Power Consumption	55 W	UV-C Radiation at 100 hr	18.7 W
Lamp Current (Nom)	0.525 A		
Voltage (Nom)	105 V		
Product Data			
Order product name	TUV PL-L 55W/4P HF 1CT/25		
Full product name	TUV PL-L 55W/4P HF 1CT/25		
Full product code	871150063379840		

TUV PL-L

Local code description	TUVPLL55WHF
Order code	927908704007
Material Nr. (12NC)	927908704007
Local order code	TUVPLL55WHF
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8711500633798
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500633804

Dimensional drawing



Product	D1 (max)	D (max)	A (max)	B (max)	C (max)
TUV PL-L 55W/4P HF 1CT/25	18 mm	38 mm	505 mm	530 mm	535 mm

Photometric data



Spectral Power Distribution Colour - TUV PL-L 55W/4P HF 1CT/25

