



TL-D LIFEMAX Super 80 JIS

TL-D 18W/830 JIS 1SL/25


The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires. The lamp is complying with Japanese Industrial Standard.

Product data

General Information		Mechanical and Housing	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Bulb Shape	T8
Life to 50% Failures (Nom)	13,000 hour(s)	Net Weight (Piece)	0.080 kg
Light Technical		Approval and Application	
Color Code	830 [CCT of 3000K]	Mercury (Hg) Content (Nom)	2.0 mg
Luminous Flux	1,450 lm	Product Data	
Color Designation	Warm White (WW)	Order product name	TL-D 18W/830 JIS 1SL/25
Correlated Color Temperature (Nom)	3000 K	Full product name	TL-D 18W/830 JIS 1SL/25
Luminous Efficacy (rated) (Nom)	80.5 lm/W	Full product code	871150028466200
Color rendering index (CRI)	82	Order code	927919983033
Operating and Electrical		Material Nr. (12NC)	927919983033
Power Consumption	18 W	Numerator - Quantity Per Pack	1
Lamp Current (Nom)	0.35 A	EAN/UPC - Product/Case	8711500284662
Voltage (Nom)	65 V	Numerator - Packs per outer box	25
Controls and Dimming		EAN/UPC - Case	8711500284679
Dimmable	No		

TL-D LIFEMAX Super 80 JIS

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/830 JIS 1SL/25	28 mm	581.3 mm	588.4 mm	585.8 mm	595.5 mm

