



MASTER TL5 High Efficiency Eco

MASTER TL5 HE Eco 25=28W/840 1SL/40

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HE Eco lamp offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A reduction in energy consumption is only achieved with current-controlled gear.
- The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information	
Cap-Base	G5
Features	na [Not Applicable]
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	2,900 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	103 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	25.2 W
Lamp Current (Nom)	0.170 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	96.600 g
Approval and Application	
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	28 kWh

MASTER TL5 High Efficiency Eco

Product Data	
Order product name	MASTER TL5 HE Eco 25=28W/840 1SL/40
Full product name	MASTER TL5 HE Eco 25=28W/840 1SL/40
Full product code	872790090820601
Order code	927990984033
Material Nr. (12NC)	927990984033


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900908206
Numerator - Packs per outer box	40
EAN/UPC - Case	8718291224716

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco 25=28W/840 1SL/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE Eco 25=28W/840 1SL/40

Lifetime




Life expectancy diagram - 3 hour cycle



Life expectancy diagram - 12 hour cycle

MASTER TL5 High Efficiency Eco

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE Eco 25=28W/840 1SL/40

